


# G35 PRO SERIES

Maximum Flow Rate: 138 l/min (36.5 USgpm)  
Maximum Pressure: 83 bar (1200 psi) for Metallic Pump Heads  
17 bar (250 psi) for Non-metallic Pump Heads

**WANNER™** HYDRA-CELL® PRO  
SEAL-LESS PUMP TECHNOLOGIES



UK  
CA CE

*G35 with Stainless Steel pump head and BSPT threaded ports.*

## A higher standard of pump performance and energy efficiency.

- Integrates **Wanner Hydra-Cell® Pro** seal-less pump technologies for the highest levels of volumetric and energy efficiencies, up to 90% across the full rpm range.
- Reliably handles a wide range of viscosities and shear sensitivities, corrosive liquids, abrasives, slurries and suspended solids.
- No mechanical dynamic seals, packing, or cups to leak, wear or replace – reduces maintenance, costs and downtime.
- Can run dry indefinitely without damage to the pump.
- Seal-less design API 674 pumps that also exceed API 675 standards for accuracy, linearity and repeatability.
- Pumped media is 100% contained – prevents degradation, contamination and environmental risks.
- Patented ADPC (Advanced Diaphragm Position Control) and hydraulic oil management system protect diaphragms under closed or restricted inlet conditions.
- Reduced ownership costs – acquisition, operation, service, maintenance, and energy use.

**WANNER™**

# G35 Pro Series | Performance

## Capacities

| Model | Max. Input<br>rpm | Max. Flow Capacities<br>@83 bar (1200 psi)<br>l/min USgpm |      | Max. Inlet Pressure |     |                    |     | Max. Discharge Pressure |      |                    |     |
|-------|-------------------|-----------------------------------------------------------|------|---------------------|-----|--------------------|-----|-------------------------|------|--------------------|-----|
|       |                   |                                                           |      | Metallic Heads      |     | Non-Metallic Heads |     | Metallic Heads          |      | Non-Metallic Heads |     |
|       |                   | bar                                                       | psi  | bar                 | psi | bar                | psi | bar                     | psi  | bar                | psi |
| G35-X | 1050              | 138                                                       | 36.5 | 34                  | 500 | 3.5                | 50  | 83                      | 1200 | 17                 | 250 |
| G35-E | 1150              | 129                                                       | 34.0 | 34                  | 500 | 3.5                | 50  | 83                      | 1200 | 17                 | 250 |

Performance and specification ratings apply to G35 configurations unless specifically noted otherwise.


\* Consult factory if operating above 83 bar (1200 psi).

## Metering & Dosing

API 675 Performance Characteristics of Steady State Accuracy  $\pm 1\%$ , Linearity  $\pm 3\%$  and Repeatability  $\pm 3\%$  can be achieved at speeds up to 960 rpm and pressures up to 69 bar (Metallic Head) and 24 bar (non-metallic pump heads)

## Available to Meet API 674

Please contact Wanner International for further information.



- True positive displacement pumping action achieves overall efficiency of  $>90\%$ , targeting improvements at lower speeds and higher pressures.

Due to the Wanner Engineering Continuous Improvement Program, specifications and other data are subject to change.

# G35 Pro Series | Specifications

## Flow Capacities @ 83 bar (1200 psi) 6-pole Motor @ 50 Hz

| Model | rpm | l/min  | USgpm |
|-------|-----|--------|-------|
| G35-X | 960 | 126.00 | 33.30 |
| G35-E | 960 | 107.00 | 28.40 |

## Flow Capacities @ 83 bar (1200 psi) 8-pole Motor @ 50 Hz

| Model | rpm | l/min | USgpm |
|-------|-----|-------|-------|
| G35-X | 730 | 95.90 | 25.30 |
| G35-E | 730 | 81.80 | 21.60 |

## Delivery @ 83 bar (1200 psi)

| Model | litres/rev | gal/rev |
|-------|------------|---------|
| G35-X | 0.1314     | 0.0347  |
| G35-E | 0.1120     | 0.0296  |

## Maximum Discharge Pressure

|                     |                                           |
|---------------------|-------------------------------------------|
| Metallic Heads:     | 83 bar (1200 psi) @ 1050 rpm max. (X cam) |
|                     | 83 bar (1200 psi) @ 1150 rpm max. (E cam) |
| Non-metallic Heads: | 17 bar (250 psi) Polypropylene            |

## Maximum Inlet Pressure

|                     |                  |
|---------------------|------------------|
| Metallic Heads:     | 34 bar (500 psi) |
| Non-metallic Heads: | 3.5 bar (50 psi) |

## Maximum Operating Temperature

|                     |                                                                                                                      |
|---------------------|----------------------------------------------------------------------------------------------------------------------|
| Metallic Heads:     | 121°C (250°F) - Consult factory for correct component selection for temperatures from 71°C (160°F) to 121°C (250°F). |
| Non-metallic Heads: | 49°C (120°F) Polypropylene                                                                                           |

## Maximum Solids Size 800 microns

## Inlet Port

|                     |                               |
|---------------------|-------------------------------|
| Metallic Heads:     | 2-1/2 inch BSPT               |
|                     | 2-1/2 inch NPT                |
|                     | 150lb or 600lb ANSI RF Flange |
|                     | 3 inch SAE                    |
| Non-metallic Heads: | 2-1/2 inch SAE J518           |

## Calculating Required Power

$$\frac{100 \times \text{rpm}}{63,000} + \frac{\text{gpm} \times \text{psi}}{1,460} = \text{electric motor hp}$$

$$\frac{100 \times \text{rpm}}{84,428} + \frac{\text{l/min} \times \text{bar}}{511} = \text{electric motor kW}$$

## Attention!

When using a variable frequency drive (VFD) controller, calculate the hp or kW at minimum and maximum pump speed to ensure the correct hp or kW motor is selected. Note that motor manufacturers typically de-rate the service factor to 1.0 when operating with a VFD.

## Calculating Pulley Size

$$\frac{\text{motor pulley OD}}{\text{pump rpm}} = \frac{\text{pump pulley OD}}{\text{motor rpm}}$$

## Discharge Port

|                     |                                |
|---------------------|--------------------------------|
| Metallic Heads:     | 1-1/4 inch BSPT                |
|                     | 1-1/4 inch NPT                 |
|                     | 600lb or 1500lb ANSI RF Flange |
|                     | 1-1/4 inch SAE                 |
| Non-metallic Heads: | 1-1/2 inch SAE J518            |

**Shaft Diameter** 50.8 mm (2 inch)

**Shaft Rotation** Reverse (bi-directional)


**Bearings** Tapered roller bearings

**Oil Capacity** 7.3 litres (7.75 US quarts)

## Weight

|                     |                     |
|---------------------|---------------------|
| Metallic Heads:     | 116.6 kg (257 lbs.) |
| Non-metallic Heads: | 87.6 kg (193 lbs.)  |

## Net Positive Suction Head (NPSHr)




## Suction Lift

Each Hydra-Cell pump has different lift capability depending on model size, cam angle, speed, and fluid characteristics. To ensure that your specific lift characteristics are met, refer to the inlet calculations regarding friction, and acceleration head losses in your Hydra-Cell Product Manual. Compare those calculations to the NPSHr curves above.


Due to the Wanner Engineering Continuous Improvement Program, specifications and other data are subject to change.

## Baseplate Assembly Long-coupled for IEC 132 Motor Frame



Dimensions in mm


G35 - IEC 132



Unit Weight Approx - 261 Kg





## Baseplate Assembly Long-coupled for IEC 160 Motor Frame




Dimensions in mm

G35 - IEC 160




Unit Weight Approx - 358 Kg

## Baseplate Assembly Long-coupled for IEC 180 Motor Frame




Dimensions in mm

G35 - IEC 180




Unit Weight Approx - 393 Kg

## Baseplate Assembly Long-coupled for IEC 200 Motor Frame



Dimensions in mm


G35 - IEC 200



Unit Weight Approx - 488 Kg





## Baseplate Assembly Long-coupled for IEC 225 Motor Frame



Dimensions in mm

G35 - IEC 225





Unit Weight Approx - 546 Kg





# G35 Pro Series | Representative Drawings

## G35 Models with BSPT Inlet/Outlet Ports mm (Inches)





## G35 Models with SAE Flange Inlet/Outlet Ports mm (Inches)





**Note:** Dimensions are for reference only. Contact factory for certified drawings.

# G35 Pro Series | Representative Drawings

## G35 Non-metallic Pump Head with SAE Flange Inlet/Outlet Ports mm (Inches)



## G35 Models with ANSI RF Flange Inlet/Outlet Ports mm (Inches)



## Valve Selection

A seal-less **C64 Pressure Regulating Valve** is recommended for Hydra-Cell G35 pumping systems, especially for high-pressure requirements or when handling dirty fluids.



A **C24 Pressure Regulating Valve** provides a capable, lower-cost alternative to C64 valves for Hydra-Cell G35 pumping systems.



**Note:** Dimensions are for reference only. Contact factory for certified drawings.

# G35 Pro Series | Options

## Contact Wanner International for:

- Motors, bases, couplings and other pump accessories
- Hydra-Oil selection and specification information
- Design considerations, installation guidelines, and other technical assistance in pump selection
- Process liquid end built with NACE and 3.1 traceable material certification



G35 with 316L Stainless Steel pump head.



G35 with Brass pump head.



G35 with Polypropylene pump head.



G35 with 316L Stainless Steel pump head and ANSI flanges.

# G35 Pro Series | How to Order

## Ordering Information

A complete G35 Series Model Number contains 12 digits including 10 customer-specified design and materials options, for example: G35XKBTHFECA.

|   |   |   |   |   |   |   |   |   |    |    |    |
|---|---|---|---|---|---|---|---|---|----|----|----|
| 1 | 2 | 3 | 4 | 5 | 6 | 7 | 8 | 9 | 10 | 11 | 12 |
|   | 3 | 5 |   |   |   |   |   |   |    |    |    |

| Digit | Order Code | Description                                                                                                                                            |
|-------|------------|--------------------------------------------------------------------------------------------------------------------------------------------------------|
| 1-3   |            | <b>Pump Configuration</b>                                                                                                                              |
|       | G35        | Shaft-driven (BSPT Ports)                                                                                                                              |
|       | D35        | Shaft-driven (NPT Ports or ANSI Flanges or SAE Flanged Ports)                                                                                          |
| 4     |            | <b>Hydraulic End Cam</b>                                                                                                                               |
|       | X          | Max 138 l/min (36.5 USgpm) @ 1050 rpm                                                                                                                  |
|       | E          | Max 129 l/min (34.0 USgpm) @ 1150 rpm                                                                                                                  |
| 5     |            | <b>Pump Head Version</b>                                                                                                                               |
|       | P          | Hydra-Cell Pro                                                                                                                                         |
|       | E          | Hydra-Cell Pro SAE Flanged Ports<br><i>See lower right for ATEX Certification Kit Options.</i>                                                         |
| 6     |            | <b>Pump Head Material</b>                                                                                                                              |
|       | B          | Brass                                                                                                                                                  |
|       | C          | Ductile Iron (Nickel-plated)                                                                                                                           |
|       | G          | Duplex Alloy 2205 Stainless Steel (with Hastelloy C followers & follower screws)                                                                       |
|       | S          | 316L Stainless Steel (Threaded or SAE Ports)                                                                                                           |
|       | N          | Polypropylene (with Hastelloy C screws & follower screws) SAE Flanges only<br><i>ATEX not available for Polypropylene pump heads.</i>                  |
|       | R          | 316L Stainless Steel ANSI flange class 150 x 600                                                                                                       |
|       | -          | 316L Stainless Steel standard manifold with custom ANSI or DIN flange options, contact Wanner International with flange specification for part number. |
| 7     |            | <b>Diaphragm &amp; O-ring Material</b>                                                                                                                 |
|       | A          | Aflas diaphragm / PTFE o-ring                                                                                                                          |
|       | E          | EPDM (requires EPDM-compatible oil - Digit 12 oil code D)                                                                                              |
|       | G          | FKM                                                                                                                                                    |
|       | J          | PTFE (available with E cam only; 960 rpm max)                                                                                                          |
|       | K          | FFKM diaphragm / PTFE o-ring                                                                                                                           |
|       | P          | Neoprene                                                                                                                                               |
|       | T          | Buna-N                                                                                                                                                 |
| 8     |            | <b>Valve Seat Material</b>                                                                                                                             |
|       | C          | Ceramic                                                                                                                                                |
|       | D          | Tungsten Carbide (900 rpm max.)                                                                                                                        |
|       | H          | 17-4 Stainless Steel                                                                                                                                   |
|       | N          | Nitronic 50                                                                                                                                            |
|       | T          | Hastelloy C                                                                                                                                            |

| Digit | Order Code | Description                                                                                |
|-------|------------|--------------------------------------------------------------------------------------------|
| 9     |            | <b>Valve Material</b>                                                                      |
|       | C          | Ceramic                                                                                    |
|       | D          | Tungsten Carbide (900 rpm max.)                                                            |
|       | F          | 17-4 Stainless Steel                                                                       |
|       | N          | Nitronic 50                                                                                |
| 10    |            | <b>Valve Springs</b>                                                                       |
|       | E          | Elgiloy                                                                                    |
|       | T          | Hastelloy C                                                                                |
| 11    |            | <b>Valve Spring Retainers</b>                                                              |
|       | C          | Celcon                                                                                     |
|       | H          | 17-7 Stainless Steel (used with metallic heads only)                                       |
|       | M          | PVDF                                                                                       |
|       | P          | Polypropylene                                                                              |
|       | T          | Hastelloy C (used with metallic heads only)                                                |
| 12    |            | <b>Hydra-Oil</b>                                                                           |
|       | A          | 10W30 standard-duty oil                                                                    |
|       | B          | 40-wt for continuous-duty oil (use with 316L SST or Hastelloy CW12MW pump head - standard) |
|       | D          | EPDM-compatible oil                                                                        |
|       | E          | Food-contact oil                                                                           |
|       | G          | 5W30 cold-temp severe-duty synthetic oil                                                   |
|       | H          | 15W50 high-temp severe-duty synthetic oil                                                  |

### G35 Pump Housing is standard as Cast Aluminum.

Upgrade to Ductile Iron available.



### ATEX Certification Kit Options

As a separate line on your order, please add the required ATEX Certification Kit Option.

- ATEX 2014/34/EU Certified, Category 2, Zone 1
- ATEX 2014/34/EU Certified, Category 3, Zone 2

- All options include Certificate, Oil Level Monitor or Sight Glass, Earth Stud & Secondary ATEX Label.
- Extra oil is required to fill the oil bowl during installation of ATEX pumps. This oil is not included and must be ordered separately.
- ATEX is not available with non-metallic pump heads.



## Partners in over 70 countries



**WANNER™**  
Global Sales and Technical Support

### Americas

- Minneapolis, Minnesota USA
- Wichita Falls, Texas USA
- São Paulo, Brazil
- Buenos Aires, Argentina

### EMEA | Australia

- Hampshire, United Kingdom
- Cairo, Egypt
- Düsseldorf, Germany
- Lyon, France

### Asia | Pacific

- Kowloon, Hong Kong
- Shanghai, China
- Jakarta, Indonesia

### India

- Mumbai, India
- New Delhi
- Bangalore
- Gujarat

## Wanner worldwide

### GLOBAL SALES & TECHNICAL SUPPORT

#### WANNER ENGINEERING, INC.

WORLD HEADQUARTERS & MANUFACTURING

Minneapolis, Minnesota USA  
t: 612-332-5681  
e: sales@wannereng.com  
Hydra-Cell.com

#### REGIONAL OFFICE

Wichita Falls, Texas USA  
t: 940-322-7111  
e: sales@wannereng.com

#### LATIN AMERICAN OFFICE

São Paulo, Brazil  
t: +55 (11) 99582-1969  
e: mmagoni@wannereng.com  
Hydra-Cell-Pumps.com.br

#### WANNER INTERNATIONAL, LTD.

UNITED KINGDOM

Church Crookham, Hampshire UK  
t: +44 (0) 1252 816847  
e: support@wannerint.com  
Hydra-Cell.co.uk

#### WANNER PUMPS, LTD.

Kowloon, HONG KONG  
t: +852 3428 6534  
e: sales@wannerpumps.com  
WannerPumps.com

Shanghai, CHINA  
t: +86-21-6876 3700  
e: sales@wannerpumps.com  
WannerPumps.com

#### WANNER INDIA PVT. LTD.

Mumbai, INDIA  
t: +91 (22) 22044766  
e: support@wannerindia.com  
WannerIndia.com

